Coupling CPS25 (L=19, D1=11 / D2=11)

For encoder with solid shaft Article number: 11065927

Overview


- Precision coupling
- Torsionally stiff coupling with low installation depth
- Pluggable
- Electrically insulating center disk
- Suitable for very high speeds




Technical data	
Technical data	
Shaft diameter D1	11 mm
Shaft diameter D2	11 mm
Operating speed	≤13500 rpm
Operating temperature	-30+80 °C
Moment of inertia	≤ 20 gcm²
Maximum torque	100 Ncm


Technical data	
Admissible parallel misalignment	≤ 0.5 mm
Admissible angular error	≤ 1 °
Weight approx.	18 g
Mechanical mounting	Clamping hub
Material	Hub: aluminium Centre disc: plastic

Dimensions





Assembly drawing



a = Admissible axial movementb = Admissible parallel misalignmentc = Admissible angular error