## FZAM 18N1155

Diffuse sensors with intensity difference

Article number: 10129023

#### Overview

- intensity difference
- 20 ... 150 mm pulsed infrared diode
- NPN
- potentiometer, 15 turn
- cable 3 pin, 2 m
- -25 ... 55 °C
- IP 65



Picture similar





| Technical data                            |                          |
|---|--------------------------|
| General data                              |                          |
| Туре                                      | Intensity difference     |
| Light source                              | Pulsed infrared diode    |
| Sensing distance Tw                       | 20 150 mm                |
| Sensing distance Tw (with doubling lense) | 30 280 mm                |
| Alignment / soiled lens indicator         | Flashing light indicator |
| Light indicator                           | LED yellow               |
| Sensitivity adjustment                    | Potentiometer, 15 turn   |
| Wave length                               | 880 nm                   |
| Suppression of reciprocal influence       | Yes                      |
| Electrical data                           |                          |
| Response time / release time              | < 0.5 ms                 |
| Voltage supply range +Vs                  | 10 30 VDC                |
| Current consumption max. (no load)        | 45 mA                    |


| Electrical data             |                          |
|-----------------------------|--------------------------|
| Current consumption typ.    | 30 mA                    |
| Voltage drop Vd             | < 1.8 VDC                |
| Output function             | Light operate            |
| Output circuit              | NPN                      |
| Output current              | < 200 mA                 |
| Short circuit protection    | Yes                      |
| Reverse polarity protection | Yes                      |
| Mechanical data             |                          |
| Width / diameter            | 18 mm                    |
| Height / length             | 50 mm                    |
| Туре                        | Cylindrical threaded     |
| Housing material            | Brass nickel plated / PC |
| Front (optics)              | PC                       |
| Connection types            | Cable 3 pin, 2 m         |
| Ambient conditions          |                          |
| Protection class            | IP 65                    |
| Operating temperature       | -25 +55 °C               |

# **FZAM 18N1155**

Diffuse sensors with intensity difference

Article number: 10129023

### **Dimension drawing**



### **Connection diagram**

