

FHDK 10P5160/S35A

Diffuse sensors with background suppression - miniature

Article number: 10151937

Overview

- background suppression
- 10 ... 30 mm
- pulsed red LED
- PNP
- mechanical, 5 turn
- connector M8 4 pin
- 25 ... 65 °C
- IP 67



Picture similar



Technical data

General data

Type	Background suppression
Version	For glass detection
Light source	Pulsed red LED
Sensing distance Tw	10 ... 30 mm
Sensing range Tb (at Tw max.)	3 ... 30 mm
Alignment / soiled lens indicator	Flashing light indicator
Light indicator	LED yellow
Sensing distance adjustment	Mechanical, 5 turn
Wave length	660 nm
Suppression of reciprocal influence	Yes

Electrical data

Response time / release time	< 1 ms
Voltage supply range +Vs	10 ... 30 VDC
Current consumption max. (no load)	30 mA

Electrical data

Current consumption typ.	20 mA
Voltage drop Vd	< 1.8 VDC
Output function	Light / dark operate
Output circuit	PNP
Output current	< 100 mA
Short circuit protection	Yes
Reverse polarity protection	Yes

Mechanical data

Width / diameter	10.4 mm
Height / length	27 mm
Depth	14 mm
Type	Rectangular
Housing material	Plastic (ASA)
Front (optics)	PMMA
Connection types	Connector M8 4 pin

Ambient conditions


Protection class	IP 67
Operating temperature	-25 ... +65 °C

FHDK 10P5160/S35A

Diffuse sensors with background suppression - miniature

Article number: 10151937

Dimension drawing



- * emitter axis

Connection diagram

