

V CXU-24C

USB 3.0, 2,3 Megapixel, Color

Article number: 11165816

Overview

- 1920 x 1200 px
- Sony IMX249
- 1/1.2" CMOS
- 38,5 fps
- USB 3.0



GEN*i*CAM



Technical data

Sensor information

Sensor	Sony IMX249 Gen1
Mono/Color	Color
Sensor type	1/1.2" CMOS
Shutter type	Global shutter
Resolution	1920 × 1200 px
Pixel size	5.86 × 5.86 µm
Exposure time	0.057 ... 60000 ms

Data quality (EMVA 1288 typical)

Dark noise	6.35 e-
Saturation capacity	31870 e-
Dynamic range	72.8 dB
Signal-to-noise ratio	45 dB
Quantum efficiency	55 % @ 465 nm 60.6 % @ 536 nm 46.5 % @ 631 nm

Acquisition formats

Image formats, interface frame rate max.	Full Frame, 1920 × 1200 px, max. 38 fps Binning 2×2, 960 × 600 px, max. 38 fps Binning 2×1, 960 × 1200 px, max. 38 fps Binning 1×2, 1920 × 600 px, max. 38 fps
Image formats, acquisition frame rate max. (Burst Mode)	Full Frame, 1920 × 1200 px, max. 38 fps Full Frame, 1920 × 1200 px, max. 38 fps Full Frame, 1920 × 1200 px, max. 38 fps

Acquisition formats

Pixel formats	BayerRG8 BayerRG10 BayerRG12 BayerRG12 Packed Mono8 Mono10 Mono12 Mono12 Packed RGB8 BGR8
---------------	--

Image preprocessing

Analog controls	Gain (0 ... 48 dB) Offset (0 ... 255 LSB 12 Bit)
Color models	Mono Raw Bayer RGB

Camera features

Basic Functions	Exposure Gain / Color Gain Trigger / Exposure Active (Flash) Binning 2x2 Partial Scan Offset Free Running Mode (Live Image)
Auto Functions	Exposure Auto Gain Auto White Balance Auto Color Transformation Auto

VCXU-24C

USB 3.0, 2,3 Megapixel, Color

Article number: 11165816

Technical data

Camera features

Image Pre-processing	Image Flipping (X/Y) Color Processing (RGB, BGR, Mono) Color Enhancement (with optimized ColorTransformationMatrix) LUT / Gamma
Acquisition / Interface	Burst Mode Adjustable Framerate Device Link Throughput Limit Internal Image Buffer
Synchronization	free running trigger
Trigger sources	Hardware Software
Trigger delay	0 ... 2 sec, tracking and buffering of up to 256 trigger signals
Process Synchronization	Events Timer Trigger Delay Debouncer Counter Sequencer Trigger via Action CMD (GigE) Additional Output Modes (e.g. Trigger Ready) Chunk data inside transferred image Encoder support via Counter End trigger source
Additional Functions	User Set Integrated temperature sensor Readable additional information (e.g. sensor information) Save Custom Data
Internal image buffer	469 MB 71 images (Trigger Mode) 1 image (Free Running Mode)

Interfaces and connectors

Data interface	USB 3.0, Transfer Rate 5000 Mbits/sec, Connector: USB 3.0 Micro B
Process interface	M8 / 8 pins (SACC-DSI-M8MS-8CON-M8-L180)
Power supply	via USB 3.0 interface

Mechanical data

Lens mount	C-mount
Width	29 mm
Height	29 mm
Depth	38 mm
Weight	≤ 90 g
Material	zinc die casting, baked varnish (until 02-2020 nickel-chrome-plated), IP 40

Electrical data

Power consumption	approx. 2,4 W @ 38 fps
Operating voltage	5 VDC (via USB3.0 interface)

Non-volatile memory

Flash memory size	128 kB
-------------------	--------

Environmental conditions

Operating temperature	0 ... +65 ° @ T = measurement point
Humidity	10 ... 90 % (non-condensing)
Protection class	IP 40

Digital I/Os

Lines	1 input line 1 output line 2 general purpose lines
-------	--

Conformity

Conformity	CE RoHS EAC
------------	-------------------

Dimension drawing

