

Overview

- M8, female, A-coded, 8-poles; PUR, shielded, 2000 cm, free cable end
- Dragchain capable
- Head A: IP65, IP67
- Cable: good resistance against chemicals, flames, oils
- Halogen free



Technical data

Side A

Head A: Connection	M8
Head A: Angle cable outlet	0°
Head A: Gender	Female
Head A: Coding	A
Head A: No. of poles	8
Head A: Tightening torque	0.2 Nm
Head A: Knurled nut material	Zinc-pressure die casting, surface Ni
Head A: Gasket material	NBR

Side B

Head B: Connection	Open-ended wires
--------------------	------------------

Cables

Cable length	2000 cm
Length tolerance	± 7.5 cm
Shielded	Yes
Conductor structure	18 × 0.1 mm
AWG	26
External sheath: Material	PUR
External sheath: Color	Black
Cable diameter	5.9 mm

Cables

Wire cross section	0.14 mm²
--------------------	----------

Electrical data

Operating voltage	max. 30 V
Operating current per contact	1.5 A

Mechanical data


Head B: Degree of protection	IP65, IP67
Bending radius (mobile)	min. 10 × outer diameter
Bending radius (fixed)	min. 5 × outer diameter
No. of bending cycles (C-track)	approx. 2000000 Cycles
Acceleration (C-track)	10 m/s²
Travel speed (C-track)	approx. 3 m/s

Environmental conditions

Temperature range (mobile)	- 25 ...+ 80 °C
Temperature range (fixed)	- 30 ...+ 80 °C
Dragchain capable	Yes
Head A: Pollution degree	3
Cable: Flame resistance	HB (UL 94)

Side A

Coding



M8	wire color	M8	wire color
1:	WH	5:	GY
2:	BN	6:	PK
3:	GN	7:	BU
4:	YE	8:	RD