Connectors and cables

Female connector M23, 16-pin




Features

- Female connector M23 with screwable nut
- With or without cable (shielded) in different lengths
- Cable version: shield is placed onto the connector housing

Part number		
10117731	Female connector M23, 16-pin, without cable (Z 131.001)	
10141369	Female connector M23, 16-pin, 10 m cable (Z 131.007)	
10142336	Female connector M23, 16-pin, 5 m cable (Z 131.005)	
11034166	Female connector M23, 16-pin, 2 m cable (Z 131.003)	

Suitable for		
GA210, GA211, GXA1W		

Technical data	
Voltage supply	<300 V
Core diameter	1.35 +0.05 mm 1.8 +0.1 mm
Cable length	2 m, 5 m, 10 m (further length upon request)
Cable type	LIY 14x0.14 mm ² / 2x0.5 mm ² (shielded cable)
Bending radius	15 x cable diameter
Outer diameter	10.1 +0.5 mm
Operating temperature	-25+105 °C
Conductor resistance	0.14 mm²: <138 Ω/km (20 °C) 0.5 mm²: <38 Ω/km (20 °C)
Material	Cable sheath: PVC grey



Terminal assignment			
Connector	Core colour		
Pin 1	violet		
Pin 2	white/brown		
Pin 3	white/green		
Pin 4	white/yellow		
Pin 5	white/grey		
Pin 6	white/pink		
Pin 7	white/blue		
Pin 8	white/red		
Pin 9	white/black		
Pin 10	brown/green		
Pin 11	green/grey		
Pin 12	blue		
Pin 13	yellow		
Pin 14	brown		
Pin 15	red		
pin 16	pink		
On the first of the control of the c			

Cores twisted in pairs: pink-yellow, violet-white/brown-green/grey, white/yellow-white/grey-white/green, white/blue-white/pink-white/red, white/black-brown/green-brown, blue-red