# **Accessories**

## **Connectors and cables**

## Female connector M12, 5-pin, A-coded



#### Features

- Female connector M12 with screwable nut
- With cable (shielded) in different lengths

Part number		
11004569	Female connector M12, 5-pin, A-coded, 10 m cable (Z 180.007)	
11034341	Female connector M12, 5-pin, A-coded, 5 m cable (Z 180.005)	
11040255	Female connector M12, 5-pin, A-coded, 2 m cable (Z 180.003)	


## Suitable for

G0P5H, GBP5H, GBP5S, GBP5W, GBU5W, GNAMG, GXP5S, GXP5W, GXP8W, GXU5W

Technical data			
Nominal voltage	60 V		
Cable length	2 m, 5 m, 10 m (further length upon request)		
Operating temperature	-25+80 °C		
Protection DIN EN 60529	IP 67 (mounted)		
Material	Cable sheath: PUR black, halogen free		

Terminal assignment		
Connector	Core colour	
Pin 1	brown	
Pin 2	white	
Pin 3	blue	
Pin 4	black	
Pin 5	grey	

## **Dimensions**





1