Accessories

Connectors and cables

Female connector M12, 12-pin, A-coded, 10 m cable



Features

- Female connector M12 with screwable nut
- With cable (shielded) in different lengths

Part number		
11052021	Female connector M12, 12-pin, A-coded, 10 m cable (Z 192.007)	

Technical data	
Core diameter	1.00 +0.05 mm
Cable length	10 m (further length upon request)
Outer diameter	8.5 mm
Operating temperature	-40+80 °C (fixed cable) -5+80 °C (moved cable)
Conductor resistance	142 Ω/km (20 °C)
Material	Cable sheath: PUR black

Terminal assignment			
Connector	Core colour	Assignment	
Pin 1	brown	UB	
Pin 2	blue	Clock+	
Pin 3	white	GND	
Pin 4	green	Data+	
Pin 5	pink	UP/DOWN inv.	
Pin 6	yellow	Data-	
Pin 7	black	DV inv.	
Pin 8	grey	Zero setting	
Pin 9	red	Clock-	
Pin 10	violet	DVMT inv.	
Pin 11	grey/pink	_	
Pin 12	red/blue	-	
	<u> </u>	<u>-</u>	

Color code according to DIN 47100.

Cores twisted in pairs: white-brown, green-yellow, grey-pink, blue-red, black-violet, grey/pink-red/blue

Dimensions



