Female connector M23, 12-pin



Features

- Female connector M23 with screwable nut
- With or without cable (shielded) in different lengths
- Cable version: shield is placed onto the connector housing
- Cable for flexible cable carriers
- Halogen-free

Part number		
11051812	Female connector M23, 12-pin, 3 m cable (Z 193.004)	
11078510	Female connector M23, 12-pin, 5 m cable (Z 193.005)	
11090860	Female connector M23, 12-pin, 8 m cable (Z 193.M08)	
11098548	Female connector M23, 12-pin, 10 m cable (Z 193.007)	

Technical data			
Voltage supply	<250 V		
Cable length	3 m, 5 m, 8 m, 10 m (further length upon request)		
Cable type	5x2x0.14 mm² / UL/CSA (shielded cable)		
Bending radius	7.5 x cable diameter		
Outer diameter	<7.3 mm		
Operating temperature	-40+70 °C		
Material	Cable sheath: PUR grey		

Terminal assignment		
Connector	Core colour	
Pin 1	brown	
Pin 2	white	
Pin 3	blue	
Pin 4	green	
Pin 5	grey	
Pin 6	yellow	
Pin 7	red	
Pin 8	black	
Pin 9	pink	
Pin 10	violet	
Pin 11-12	_	

Color code according to DIN 47100. Cores twisted in pairs: white-brown, green-yellow, grey-pink, blue-red, black-violet

1

Dimensions

