## Female connector M23, 12-pin



## **Features**

- Female connector M23 with screwable nut
- With cable (shielded) in different lengths
- Cable version: shield is placed onto the connector housing
- Cable for flexible cable carriers
- Halogen-free
- UL/CSA certified

Part number		
11089005	Female connector M23, 12-pin, 5 m cable (Z 195.M05)	
11215585	Female connector M23, 12-pin, 10 m cable (Z 195.M10)	

Technical data			
Voltage supply	<250 V		
Cable length	5 m, 10 m (further length upon request)		
Cable type	UNITRONIC-FD CP (TP) plus UL/CSA 6x2x0.14 mm² (shielded, twisted pair)		
Bending radius	7.5 x cable diameter		
Outer diameter	7.5 mm		
Operating temperature	-40+70 °C		
Material	Cable sheath: PUR grey		

Terminal assignment		
Connector	Core colour	
Pin 1	brown	
Pin 2	white	
Pin 3	blue	
Pin 4	green	
Pin 5	grey	
Pin 6	yellow	
Pin 7	red	
Pin 8	red/blue	
Pin 9	pink	
Pin 10	violet	
Pin 11	black	
Pin 12	grey/pink	

Color code according to DIN 47100.

Cores twisted in pairs: white-brown, green-yellow, grey-pink, blue-red, black-violet, grey/pink-red/blue

## **Dimensions**

