

LIVE MONITOR			
	▽		
MEAS TYPE		Avg DIST Max DIST Min DIST	
	△ ▽		
OBJECT		Bright Dark	
	△ ▽		
PRECISON		Standard High Very High	
	△ ▽		
FIELD OF VIEW		LIMIT LEFT LIMIT RIGHT Set max values	Value in mm Value in mm
	△ ▽		
ANALOG OUT		SCALE OUT DIST NEAR DIST FAR Set max values ANALOG OUT CHARACTERISTIC	Value in mm Value in mm
	△ ▽		
DIGITAL OUT		DIGITAL OUT SWITCH POINT WINDOW P1 WINDOW P2 OUTPUT LEVEL	Point / Window Value in mm Value in mm Value in mm Active high / Active low
	△ ▽		
SYSTEM		RS485 BAUD RS485 ADDR DISPLAY LIGHT SENSOR INFO LANGUAGE RESET	38400 57600 115200 number OFF 5min OFF 10min OFF 20min Always ON SENSOR TYPE SERIAL NUM English Deutsch Inglese Français Factory Set
	△ ▽		
SETTINGS		APPLY STORE SHOW ACTIVE SHOW SETTING 1 SHOW SETTING 2 SHOW SETTING 3	Setting 1 Setting 2 Setting 3 Setting 1 Setting 2 Setting 3 Values Values Values Values
	△		

