

Overview

- M5, female, A-coded, 4-poles; PUR, 1000 cm; M8, male, 4-poles
- Head A: IP67; Head B: IP67



Technical data

Side A

Head A: Connection	M5
Head A: Angle cable outlet	0°
Head A: Gender	Female
Head A: Coding	A
Head A: No. of poles	4
Labeling sleeve side A	No

Side B

Head B: Connection	M8
Head B: Angle cable outlet	0°
Head B: Gender	Male
Head B: No. of poles	4
Labeling sleeve side B	No

Cables

Cable length	1000 cm
Length tolerance	± 15 cm
Shielded	Yes
Conductor structure	18 × 0.1 mm
AWG	26

Cables

External sheath: Material	PUR/PVC
External sheath: Color	Black
Cable diameter	4.0 mm
Wire cross section	0.14 mm²

Electrical data

Operating voltage	60 V
-------------------	------

Mechanical data


Head A: Degree of protection	IP67
Head B: Degree of protection	IP67
Bending radius (mobile)	approx. 10 × outer diameter
Bending radius (fixed)	approx. 5 × outer diameter

Environmental conditions

Cable: Temperature range (fixed)	- 25 ...+ 80 °C
Head A: Pollution degree	3
Head B: Pollution degree	3


Side A

Technical drawing




Side A

Coding



Side B


Technical drawing



Dimension drawing



Coding



Connection diagram

