

Overview

- Female straight
- M8 , 4-pole, A-coded
- 0,14 - 0,5mm², 4 - 5,5mm, shielded



Technical data

Side A		Side A	
Head A: Connection	M8	Cable diameter (max.)	5.5 mm
Head A: Angle cable outlet	0°	Cable diameter (min.)	4 mm
Head A: Gender	Female	Electrical data	
Head A: Shielded	Yes	Operating voltage	max. 50 V DC
Head A: No. of poles	4	Operating current per contact	max. 4 A
Head A: Tightening torque	0.4 Nm	Mechanical data	
Min. AWG	26	Head A: Degree of protection	IP67
Max. AWG	20	Environmental conditions	
Connection method	Screw terminals	Head A: Pollution degree	3
Wire cross section (max.)	0.5 mm ²		
Wire cross section (min.)	0.14 mm ²		