

Cable GigE M12X/RJ45, STP, 10.0m, flex, 90°

Article number: 11195122

overview

- Gigabit Ethernet interface cable
- CAT6A
- M12/8-pin connector, X-coded (screw lock), 90° angled to RJ45
- cable carrier compatible
- suitable for robotic applications (+/- 180°/ 0.5 m, min. 1.000.000 torsion cycles)
- length 10,0 m



technical data

electrical data

number of poles	8
connectors	M12/x-kodiert, gewinkelt, verschraubbar RJ45

mechanical data

bending radius static	70 mm
bending cycles	1000000
use in cable carriers	yes, flexible cable
cable length [m]	10 m

mechanical data

weight	≤ 700 g
material	TPU, halogen-free


interface

data interface	10 GigE GigE
----------------	-----------------


environmental conditions

conformity	RoHS CE
protection class	IP 67 (camera side)

dimension drawing



pin assignment



M12	RJ45	M12	RJ45
1:	1	7:	5
2:	2	8:	4
3:	3	5:	7
4:	6	6:	8