

Cable GigE RJ45s/RJ45, 20,0 m, flex v2

Article number: 11173257


Overview


- Gigabit Ethernet interface cable
- CAT5e
- RJ45 (screw lock) to RJ45
- suitable for cable carrier and torsion applications
- length 20,0 m



Technical data				
Electrical data		Mechanical data		
Number of poles	8	Cable length [m]	20 m	
Connectors	RJ45, screw lock RJ45	Weight	≤ 1600 g	
		Material	PVC, lead-free	
Mechanical data		Interface		
Smallest bending radius	42 mm	Data interface	GigE	
static		Environmental conditions		
Bending cycles	10000000	Flame resistance	Flame resistance UL20276 80°C / 30V	
Use in cable carriers	yes	Traine recicianes	0220270 00 07 00 0	

Pin assignment





RJ45S RJ45		RJ45S RJ45		
1:	1	5:	5	
2:	2	6:	6	
3:	3	7:	7	
4:	4	8:	8	