


Connection cable connector M23 (CW) / connector

D-SUB, 0.2 m

Article number: 11119257

Overview

- Connecting cable shielded with connector M23, 12-pin, female contacts, clockwise (CW) on connector D-SUB, 9-pin, male contacts



Technical data

Cable specifications

Weight approx.	115 g
Cable length	0.2 m
Operating temperature	-10...+60 °C

Cable specifications


Outer diameter	≈ 7,5 mm
Connection	Connector M23, 12-pin Connector D-SUB, 9-pin
Shield	Common low capacity shield

Terminal assignment


Connector M23	Connector D-SUB
Pin 5	Pin 1
Pin 6	Pin 6
Pin 8	Pin 2
Pin 1	Pin 7
Pin 3	Pin 3
Pin 4	Pin 8
Pin 12	Pin 4
Pin 10	Pin 5
Pin 2	NC
Pin 11	NC
Pin 9 (NC)	Pin 9 (NC)
Pin 7	NC
Housing/Shield	Housing/Shield

Suitable for

PC-Programming Tool Z-PA-EI-P, Handheld Programming Tool Z-PA-EI-H, EIL580P-B, EIL580P-SC, EIL580P-SY, EIL580P-T



Connector M23, female, 12-pin, clockwise (CW)



Connector D-SUB, pin contacts, 9-pin

Dimensions

