

# Connection cable with connector M23 / rear mount socket M23 (S2BG12/H2SG12), 2 m

Article number: 11078200

## Overview

- Shielded connection cable with M23-female connector (12-pin) and rear mount socket M23 (male, 12-pin)



## Technical data

### Cable specifications

Material	Cable sheath: PUR black
Weight approx.	310 g
Cable length	2 m
Operating temperature	-40...+100 °C (fixed cable) -25...+100 °C (moved cable)

### Cable specifications

Outer diameter	≈ 7.5 mm
Connection	Connector M23, 12-pin Rear mount socket M23 (male, 12-pin)

## Terminal assignment

Connector S2BG12	Rear mount socket H2SG12
Pin 5	Pin 5
Pin 6	Pin 6
Pin 8	Pin 8
Pin 1	Pin 1
Pin 3	Pin 3
Pin 4	Pin 4
Pin 12	Pin 12
Pin 10	Pin 10
Pin 2	Pin 2
Pin 11	Pin 11
Pin 7 (NC)	Pin 7 (NC)
Pin 9 (NC)	Pin 9 (NC)
Housing/Shield	Housing/Shield

## Dimensions

connector type 2, bush contacts, straight, 12-pin, EMV S2BG12

rear mount socket type 2, pin contacts, straight, 12-pin, EMV H2SG12

