

### Overview

- M5, Female, A-coded, 3-poles; PUR, 500cm, free cable end
- Head A: IP67
- Halogen free



### Technical data

#### Side A

Head A: Connection	M5
Head A: Angle cable outlet	90°
Head A: Gender	Female
Head A: Coding	A
Head A: No. of poles	3
Head A: LED	No
Head A: Body color	Black

#### Side B

Head B: Connection	Open-ended wires
--------------------	------------------

#### Cables

Cable length	500 cm
Stripping length	0 mm
Shielded	No
Conductor structure	18 × 0.1 mm
AWG	26
External sheath: Material	PUR
External sheath: Color	Black
Cable diameter	3.4 mm

#### Electrical data

Operating voltage	300 V
Operating voltage (only UL listed)	300 V

#### Mechanical data


Head A: Degree of protection	IP67
Bending radius (mobile)	min. 10 × outer diameter
Bending radius (fixed)	min. 3 × outer diameter
No. of bending cycles (C-track)	min. 1000000 Cycles
Acceleration (C-track)	max. 2 m/s <sup>2</sup>
Travel speed (C-track)	max. 0.83 m/s

#### Environmental conditions

Temperature range (mobile)	- 30 ...+ 85 °C
Temperature range (fixed)	- 40 ...+ 85 °C
Cable: Temperature range (fixed)	- 25 ...+ 80 °C
Dragchain capable	No
Head A: Pollution degree	3


### Side A

#### Technical drawing



### Side A

#### Coding



- 1 braun
- 2 nicht konfektioniert
- 3 blau
- 4 schwarz

**Dimension drawing**

