

Overview

- Diffuse sensors
- side view
- -30 ... 70 °C



Picture similar



Technical data

General data

Particular characteristics	Side view
Type	Diffuse sensors
Sensing distance Tw	1 ... 265 mm
Response time / release time	0.05 ... 5 ms
Type of head (fiber optic cable)	Rectangular, side view
Width / diameter (head)	20.6 mm
Height / length (head)	20.6 mm

General data

Depth (head)	5 mm
Material (head)	POM
Bending radius	15 mm
Cable jacket diameter	2.2 mm
Material cable jacket	PE
Material (fiber optic cable)	Plastic
Length (fiber optic cable)	2000 mm
Operating temperature	-30 ... +70 °C

Remarks

- Reliably detects small, thin or vibrating workpieces in an area of 10,85 mm.

Dimension drawing

