

Fiber Optical Cable XSsh/LC, IP67, 20,0m

Article number: 11213911

overview

- Fiber Optical cable for 10-GigE connection, multi mode
- SFP+ module to SFP+ module (SFP+ modules are not included and have to be ordered separately)
- high robustness - crush resistance 2100 N/cm
- length 20.0m
- IP65/67 in combination with "Housing Cable Adapter SFP+/IP67"



technical data

electrical data

connectors SFP+

mechanical data

external diameter 6,5 mm

bending radius static 104 mm

bending radius moved in-
stallation 52 mm

use in cable carriers no

cable length [m] 20 m

weight ≤ 720 g

material PUR
TPE

interface

data interface 10 GigE

environmental conditions

operating temperature -40 ... -85 °C

conformity RoHS with exception (6(b) / 6(b)-II: Lead as an alloying element in aluminium containing up to 0.4 % lead by weight / Lead as an alloying element in aluminium for machining purposes with a lead content up to 0.4 % by weight)

protection class IP 65/67 (camera side)