


overview

- Ethernet cable for robotic applications
- M12/4-pin male connector to RJ45
- length 10.0 m



technical data

electrical data

transfer category	CAT5E
shielding	yes
number of poles	4
connectors	M12 male connector, screw lock RJ45

mechanical data

bending radius static	58,8
bending radius moved in- stallation	79,2 mm
use in cable carriers	yes, flexible cable
cable length [m]	10 m
conductor cross-section	4 × 0,34mm ²

mechanical data

weight	≤ 700 g
material	PUR, halogen-free

interface

data interface	Ethernet
----------------	----------

environmental conditions

operation temperature (static)	-40 ... +80 °C
operation temperature (moved installation)	-20 ... +60 °C
conformity	CE RoHS UL (in preparation)