

# MSFS AA03X08

Magnetic rotor for bearingless encoder

Article number: 11016706

## Overview

- Simple screw mounting
- For 6 mm shaft diameter
- Operating temperature -40...+125 °C



## Technical data

### Technical data

Dimensions	ø16 x 22 mm
Bore	ø6 mm
Sensing	On-axis magnet
Number of poles	2

### Technical data

Mounting type	Screw mounting
Operating temperature	-40...+125 °C
Weight approx.	14 g
Material	Samarium-Cobalt Hub: aluminium

## Dimensions

