

**overview**

- Gigabit Ethernet PCI Express interface board
- Gigabit Ethernet cable 3,0 m
- process interface cable 0,15 m
- international power supply 24V/1,0A
- MXG Heat Sink Kit
- MX C-mount kits (mono and color)
- Software (WINDOWS, LINUX, LINUX ARM) via Download
- camera not included



**technical data**

**C-mount kit**

article number	Mono: 11097369 Color: 11097380
name	MX C-Mount Kit
components	<ul style="list-style-type: none"> <li>• C-mount adapter, sealings, screws, retaining bracket, spacers, cover glass and IR filter</li> </ul>

**cable**

article number	10170048
name	cable GigE RJ45/RJ45, 3,0 m
features	<ul style="list-style-type: none"> <li>• GigE cable</li> <li>• RJ45/RJ45</li> <li>• CAT7</li> <li>• length 3,0 m</li> </ul>

**heat sink kit**

article number	11098288
name	MXG Heat Sink Kit
components	<ul style="list-style-type: none"> <li>• Heat sink for MXG board level cameras incl. screws, retaining bracket and thermal conductive pads</li> </ul>

**process interface cable**

article number	11098762
name	cable 8 wires, 0,15 m (Z-ESG JSFV0015)
features	<ul style="list-style-type: none"> <li>• cable</li> <li>• JST crimp connector</li> <li>• female</li> <li>• 8-pin</li> <li>• open wires at one side</li> <li>• AWG32</li> <li>• length 0,15 m</li> </ul>

**interface card**

article number	11137188
name	PCIe Ethernet Server Adapter I210-T1 (ZVA-PCIe_Intel_Eth_Server_Adptr_I1210-T1)
features	<ul style="list-style-type: none"> <li>• 1 port GigE to PCI Express host adapter</li> <li>• RJ45 connector</li> <li>• chipset: Intel® i210 Gigabit Controller</li> <li>• tested Jumbo Frames: 9 kByte</li> <li>• x1 lane interface</li> </ul>

**power supply**

article number	11102189
name	power supply 24V/1,0A int. MXG
features	<ul style="list-style-type: none"> <li>• power supply 24V/1,0A international for Baumer MX cameras</li> <li>• adapter for EU, US, UK, AU and KR</li> </ul>