

# Obj Cinegon 1,4/12-0906

Article number: 10170038

## Overview

- Schneider Kreuznach lens
- 12 mm
- F 1,4-11
- format 2/3"
- M.O.D. 0,614 m
- C-mount



## Technical data

### General data

Manufacturer Schneider Kreuznach

### Mechanical data

Lens mount C-mount

Dimensions 34 mm × 48,5 mm

Max. outer diameter 34 mm (without knurled screws)  
44 mm (with knurled screws)

Max. length (excl. thread) 42.7 mm

Weight ≤ 99 g

Filter thread M 30,5 × 0,5

### Lens data

Lens resolution 5 MP

Focal length 12 mm

Focal range ≥ 12 mm ... < 25 mm

Format 2/3"

Aperture F1,4-11

Aperture control Manual

M.O.D. 0.614 m

### Environmental conditions

Storage temperature -25 ... +70 °C