

Obj Kowa LM12XC 12mm/f2,0

Article number: 11092574

overview

- Kowa lens
- 12 mm
- F 2,0-22
- format 4/3"
- M.O.D. 0,1 m
- C-mount



technical data

general data

manufacturer Kowa

mechanical data

lens mount C-mount

dimensions 57 mm × 85 mm

max. outer diameter 57 mm (without knurled screws)
67 mm (with knurled screws)

max. length (excl. thread) 85 mm

weight ≤ 270 g

filter thread M 55,0 × 0,75

lens data

lens resolution 26 MP

focal length 12 mm

lens data

focal range ≥ 12 mm ... < 25 mm

format 4/3"

aperture F2,0-22

aperture control manual

M.O.D. 0,1 m

horizontal angle of view 74,9 °

vertical angle of view 59,6 °

diagonal angle of view 86,8 °

at image format 13,8 × 18,4 mm

environmental conditions

operating temperature -10 ... +50 °C