

Obj Kowa LM16HC 16mm/f1,4

Article number: 11092601

overview

- Kowa lens
- 16 mm
- F 1,4-16
- format 1"
- M.O.D. 0,3 m
- C-mount



technical data

general data

manufacturer Kowa

mechanical data

lens mount C-mount

dimensions 42 mm × 52,9 mm

max. outer diameter 43 mm (without knurled screws)
53 mm (with knurled screws)

max. length (excl. thread) 52,9 mm

weight ≤ 140 g

filter thread M 35,5 × 0,5

lens data

lens resolution 7 MP

focal length 16 mm

lens data

focal range ≥ 12 mm ... < 25 mm

format 1"

aperture F1,4-16

aperture control manual

M.O.D. 0,3 m

horizontal angle of view 44,3 °

vertical angle of view 33,6 °

diagonal angle of view 54,4 °

at image format 12,8 × 9,6 mm

environmental conditions

operating temperature -10 ... +50 °C