

Obj Kowa LM16XC 16mm/f2,0

Article number: 11092592

overview

- Kowa lens
- 16 mm
- F 2,0-22
- format 4/3"
- M.O.D. 0,1 m
- C-mount



technical data

general data

manufacturer Kowa

mechanical data

lens mount C-mount

dimensions 45 mm × 79,5 mm

max. outer diameter 45 mm (without knurled screws)
55 mm (with knurled screws)

max. length (excl. thread) 79 mm

weight ≤ 250 g

filter thread M 40,5 × 0,5

lens data

lens resolution 26 MP

focal length 16 mm

lens data

focal range ≥ 12 mm ... < 25 mm

format 4/3"

aperture F2,0-22

aperture control manual

M.O.D. 0,1 m

horizontal angle of view 60,6 °

vertical angle of view 47,2 °

diagonal angle of view 72 °

at image format 13,8 × 18,4 mm

environmental conditions

operating temperature -10 ... +50 °C