

Obj Kowa LM16XC 16mm/f2,0

Article number: 11092592

Overview

- Kowa lens
- 16 mm
- F 2,0-22
- format 4/3"
- M.O.D. 0,1 m
- C-mount



Technical data

General data

Manufacturer Kowa

Mechanical data

Lens mount C-mount

Dimensions 45 mm × 79,5 mm

Max. outer diameter 45 mm (without knurled screws)
55 mm (with knurled screws)

Max. length (excl. thread) 79 mm

Weight ≤ 250 g

Filter thread M 40,5 × 0,5

Lens data

Lens resolution 26 MP

Pixel resolution 3 μm

Lens data

Focal length 16 mm

Focal range ≥ 12 mm ... < 25 mm

Format 4/3"

Aperture F2,0-22

Aperture control Manual

M.O.D. 0.1 m

Horizontal angle of view 60.6 °

Vertical angle of view 47.2 °

Diagonal angle of view 72 °

At image format 13,8 × 18,4 mm

Environmental conditions

Operating temperature -10 ... +50 °C