

# Obj Kowa LM25XC 25mm/f2,0

Article number: 11092593

## overview

- Kowa lens
- 25 mm
- F 2,0-16
- format 4/3"
- M.O.D. 0,15 m
- C-mount



## technical data

### general data

manufacturer Kowa

### mechanical data

lens mount C-mount

dimensions 45 mm × 89 mm

max. outer diameter 45 mm (without knurled screws)  
55 mm (with knurled screws)

max. length (excl. thread) 89 mm

weight ≤ 250 g

filter thread M 40,5 × 0,5

### lens data

lens resolution 26 MP

focal length 25 mm

### lens data

focal range ≥ 25 mm ... < 50 mm

format 4/3"

aperture F2,0-16

aperture control manual

M.O.D. 0,15 m

horizontal angle of view 40,9 °

vertical angle of view 31,1 °

diagonal angle of view 50,2 °

at image format 13,8 × 18,4 mm

### environmental conditions

operating temperature -10 ... +50 °C