


# Obj Kowa LM50XC 50mm/f2.0

Article number: 11166201

## overview

- Kowa lens
- 50 mm
- F 2,0-22
- format 4/3"
- M.O.D. 0,3 m
- C-mount



## technical data

### general data

manufacturer Kowa

### mechanical data

lens mount C-mount

dimensions 44 mm × 78 mm

max. outer diameter 44 mm (without knurled screws)  
55 mm (with knurled screws)

max. length (excl. thread) 78 mm

weight ≤ 220 g

filter thread M 37,5 × 0,5

### lens data

focal length 50 mm

### lens data

focal range ≥ 50 mm

format 4/3"

aperture F2,0-22

aperture control manual

M.O.D. 0,3 m

horizontal angle of view 14,5 °

vertical angle of view 10,8 °

diagonal angle of view 18 °

at image format 12,8 × 9,6 mm

### environmental conditions

operating temperature -10 ... +45 °C