

Obj Kowa LM8JC10M 8,5mm/1,8

Article number: 11091819

Overview

- Kowa lens
- 8,5 mm
- F 1,6-22
- format 2/3"
- M.O.D. 0,1 m
- locating screw for aperture and focus
- C-mount



Technical data

General data

Manufacturer Kowa

Mechanical data

Lens mount C-mount

Dimensions 36 mm × 56 mm

Max. outer diameter 36 mm (without knurled screws)
46 mm (with knurled screws)

Max. length (excl. thread) 56 mm

Weight ≤ 115 g

Filter thread M 34,0 × 0,5

Lens data

Lens resolution 9 MP

Focal length 8.5 mm

Lens data

Focal range < 12 mm

Format 2/3"

Aperture F1,8-22

Aperture control Manual

M.O.D. 0.1 m

Horizontal angle of view 54 °

Vertical angle of view 41.9 °

Diagonal angle of view 64.6 °

At image format 6,6 × 8,8 mm

Environmental conditions

Operating temperature -10 ... +50 °C