

Obj LINOS MeVis C 25mm/f1,6

Article number: 11051404

Overview

- Linos lens
- 25 mm
- F 1,6-16
- format 1"
- M.O.D. 0,26 m
- C-mount



Technical data

General data

Manufacturer Linos

Mechanical data

Lens mount C-mount

Dimensions 42 mm × 44,1 mm

Max. outer diameter 42 mm (without knurled screws)
52 mm (with knurled screws)

Max. length (excl. thread) 44.1 mm

Weight ≤ 156 g

Filter thread M 35,5 × 0,5

Lens data

Lens resolution 20 MP

Focal length 25 mm

Focal range ≥ 25 mm ... < 50 mm

Format 1"

Aperture F1,6-16

Aperture control Manual

M.O.D. 0.26 m