


overview

- Schneider Kreuznach lens
- 28 mm
- F 2,0-11
- format 1.3"
- M.O.D. 0,064 m
- C-mount
- Phase-Out starting 08/20, alternative via sales



technical data

general data

manufacturer Schneider Kreuznach

mechanical data

lens mount C-mount

dimensions 34 mm × 38,5 mm

max. outer diameter 34 mm (without knurled screws)
44 mm (with knurled screws)

max. length (excl. thread) 34,7 mm

weight ≤ 122 g

filter thread M 30,5 × 0,5

lens data

lens resolution 5 MP

focal length 28 mm

focal range ≥ 25 mm ... < 50 mm

format 1.3"

aperture F2,0-11

aperture control manual

M.O.D. 0,064 m

environmental conditions

storage temperature -25 ... +70 °C