

overview

- universal power supply 24V/1,0A international with adapters for EU, US, UK, AU, KR
- for MXG



technical data

electrical data

input	adapter: EU, US, UK, AU, KR (changeable)
input voltage	90 VAC .. 264 VAC
frequency	47 Hz .. 63 Hz
output	JST-3pin Plug (SHR-03V-S-B)
operating voltage	24 VDC
current	1 A
tolerance	5 %
ripple	240 mV p-p
level of efficiency	Level V

electrical data

max. performance	24 W
------------------	------

mechanical data

dimensions	93,5 × 46,0 × 36,2 mm
cable length [m]	1,6 m
weight	≤ 170 g
material	plastic

environmental conditions

operating temperature	0 ... +40 °C
storage temperature	-20 ... +85 °C
humidity	8 ... 90 % (non-condensing)