

overview

- power supply 24V/1,0A with adapters for EU, US, UK AU, KR
- in combination with "Cable power adapter M12/DC connector" (11048083) suitable for VCXG.I(.XT), VLXT and VeriSens



technical data

electrical data

input	adapter: EU, US, UK, AU, KR (changeable)
input voltage	90 VAC .. 264 VAC
frequency	47 Hz .. 63 Hz
output	DC Plug 5,5 x 2,1 mm
operating voltage	24 VDC
current	1 A
tolerance	5 %
ripple	240 mV p-p
level of efficiency	Level V

electrical data

max. performance	24 W
------------------	------

mechanical data

dimensions	93,5 mm × 46,0 mm × 36,2 mm
cable length [m]	5 m
weight	≤ 170 g
material	plastic

environmental conditions

operating temperature	0 ... +40 °C
storage temperature	-20 ... +85 °C
humidity	8 ... 90 % (non-condensing)