

overview

- industrial DIN rail power supply 24V/60W
- for TX, VisiLine, VisiLine IP, MXG, SX and HX cameras (except HXC13)
- Phase-Out starting 08/20, alternative via sales



technical data

electrical data

input	screw clamp
input voltage	85 VAC .. 264 VAC
frequency	47 Hz .. 63 Hz
output	screw clamp (2 outputs)
operating voltage	24 VDC
current	2,5 A
ripple	150 mV p-p
level of efficiency	Level V

electrical data

max. performance	60 W
------------------	------

mechanical data

dimensions	40,0 mm × 90,0 mm × 100,0 mm
weight	≤ 330 g
material	plastic

environmental conditions

operating temperature	0 ... +40 °C
storage temperature	-20 ... +85 °C
humidity	8 ... 90 % (non-condensing)