

**overview**

- universal power supply 12V/2,0A international with adapters for EU, US, UK, AU, KR
- power supply and process interface adapter cable for VisiLine cameras, length 5,0 m



**technical data**

**electrical data**

input	adapter: EU, US, UK, AU, KR (changeable)
input voltage	90 VAC .. 264 VAC
frequency	47 Hz .. 63 Hz
output	DC Plug 5,5 x 2,1 mm
operating voltage	12 VDC
current	2 A
tolerance	5 %
ripple	120 mV p-p
level of efficiency	Level V

**electrical data**

max. performance 24 W

**mechanical data**

dimensions	93,5 mm × 46,0 mm × 36,2 mm
cable length [m]	1,8 m
weight	≤ 170 g
material	plastic

**environmental conditions**

operating temperature	0 ... +40 °C
storage temperature	-20 ... +85 °C
humidity	8 ... 90 % (non-condensing)