

overview

- confectioned connection cable M12/12-pin with power supply 24V/1.0A
- Ethernet cable
- 90° angled fixation bracket incl. screws
- screw driver
- Application Suite (Windows) via Download
- VeriSens not included



technical data

fixing

article number	11177010
name	ZVM-VS_Mounting Adapter
features	<ul style="list-style-type: none"> • 90° angled fixation bracket incl. screws

cable

article number	11048502
name	Ethernet cable, 2,0 m (KSG 34A/KSG45AP0200G/E)
features	<ul style="list-style-type: none"> • Ethernet cable • M12/4-pin • shielded • straight RJ45 connector • length 2,0 m

process interface cable

article number	11048083
----------------	----------

process interface cable

name	Cable power adapter M12/DC connector
features	<ul style="list-style-type: none"> • connecting cable • M12/12-pin • shielded • straight connector • length 2,0 m • confectioned DC connector

other

tools	screw driver I6K (Torx) 3 mm for VeriSens mounting and focal adjustment
-------	-------------------------------------------------------------------------

power supply

article number	11079750
name	power supply 24V/1,0A int. VeriSens
features	<ul style="list-style-type: none"> • power supply 24V/1.0A • adapter for EU, US, UK, AU and KR