

Hand-held piece counter

With metal housing

Display 4-digits, reset button

T 123



T 123 for table mount

Features

- Hand-held counter to count persons or pieces
- Inventory
- In production processes
- Traffic recording
- In cinemas, on sports grounds, at ski lifts

Technical data - mechanical design

Function	Hand-held piece counter, table mount
Display	White numbers on black
Number of digits	4-digits
Digit height	4.5 mm
Zero setting	Reset by knurled knob
Count mode	1 button touch = 1 count
Measuring range	9999
Ambient temperature	0...+60 °C
Housing type	Housing with ground plate (table mount)
Housing colour	Silver
Dimensions mounting plate	ø65 mm
Mounting type	Base / mounting plate with 3 holes
Weight approx.	190 g
Material	Zinc/die-cast alloy

Hand-held piece counter

With metal housing

Display 4-digits, reset button

T 123

Part number

T 123.010 **A**

Housing
A With plate for table mount

Dimensions

