

Accessories

		Hygienic adapters for „Process connection“ A030 (G 1/2 A hygienic, BCID: A03)	
		Description	Ordering information
		DIN 11851 (dairy pipe connection)	
		DN 25, AISI 316L (1.4404)	ZPH3-3221
		DN 40, AISI 316L (1.4404)	ZPH3-3224
		DN 50, AISI 316L (1.4404)	ZPH3-3225
		SMS 1145	
		DN 51, AISI 316L (1.4404)	ZPH1-3236
		DIN 11864-1-A (aseptic screwed union)	
		DN 40, AISI 316L (1.4404)	ZPH3-3254
		DN 50, AISI 316L (1.4404)	ZPH3-3255
		Baumer Hygienic Connection	
		BHC 3A DN 38, AISI 316L (1.4404)	ZPH1-32D3
		Thread adapters for „Process connection“ A030 (G 1/2 A hygienic, BCID: A03)	
		Description	Ordering information
		Industry standard	
	G 1 A ISO 228-1, AISI 316L (1.4404)	ZP11-32B	
	G 1 1/2 A ISO 228-1, AISI 316L (1.4404)	ZP11-32D	
	G 2 A ISO 228-1, AISI 316L (1.4404)	ZP11-32E	
	1-11 1/2 NPT, AISI 316L (1.4404)	ZP11-32G	
		Vibration fork replacement	
		G 3/4 A ISO 228-1 (EH FTL GQ2), AISI 316L (1.4404)	ZPH1-32BA
		G 3/4 A ISO228-1 (VS Ø 21.3), AISI 316L (1.4404)	ZPH1-32BC
		G 1 A ISO 228-1 (EH FTL GW2), AISI 316L (1.4404)	ZPH1-32CB
		G 1 A ISO228-1 (VS Ø 21.3), AISI 316L (1.4404)	ZPH1-32CD
		Hygienic interfacing	
		G 1 A hygienic, AISI 316L (1.4404)	ZPH1-32C0

TER8

Front-flush and low-invasive resistance thermometers

Accessories

Blind plugs

Description

Ordering information

Blind plugs

G 1/2 A hygienic, AISI 316L (1.4404)

ZPX5-32



Welding mandrels for threaded hygienic welded connections

Description

Ordering information

Welding mandrels

G 1/2 A hygienic, Brass

ZPX6-36



Hygienic connectors with stainless steel knurl, protection up to IP69K (M12-A, 4-pin, BCID: X04)

Description

Ordering information

Female connector straight with attached cable

2 m, TPE
5 m, TPE
10 m, TPE
25 m, TPE

ESG 34AY0200
ESG 34AY0500
ESG 34AY1000
ESG 34AY2500



Female connector angular with attached cable

2 m, TPE
5 m, TPE
10 m, TPE
25 m, TPE

ESW 33AY0200
ESW 33AY0500
ESW 33AY1000
ESW 33AY2500



TER8

Front-flush and low-invasive resistance thermometers

Accessories

Industrial connectors, protection up to IP67 (M12-A, 4-pin, BCID: X04)

Description

Ordering information



Female connector straight with attached cable

2 m, PUR
5 m, PUR
10 m, PUR

ESG 34AH0200
ESG 34AH0500
ESG 34AH1000



Female connector angular with attached cable

2 m, PUR
5 m, PUR
10 m, PUR
15 m, PUR
20 m, PUR

ESW 33AH0200
ESW 33AH0500
ESW 33AH1000
ESW 33AH1500
ESW 33AH2000



Female connector straight with attached cable, shielded

2 m, PUR
5 m, PUR
10 m, PUR

ESG 34AH0200G
ESG 34AH0500G
ESG 34AH1000G



Female connector angular with attached cable, shielded

2 m, PUR
5 m, PUR
10 m, PUR

ESW 33AH0200G
ESW 33AH0500G
ESW 33AH1000G



Female connector straight with screw terminals

PG7, PBT

ES 18A PG7



Female connector angular with screw terminals


PG7, PBT

ES 14A PG7

Interfaces

Description

Ordering information



FlexProgrammer 9701

Kit for sensor parameterization, including programming interface with USB, connecting cables, carrying strap, CD-ROM with PC software and DTM drivers

9701-0001