

**Overview**

- USB 3.0 PCIe interface board (2 ports)
- USB 3.0 cable, 3,0 m
- process interface cable 5,0 m
- Mounting Adapter Type E
- Software (WINDOWS, LINUX, LINUX ARM) via Download
- camera not included



Picture similar

**Technical data**

**Fixing**

Article number	11165173
Name	Mounting Adapter Type E
Features	<ul style="list-style-type: none"> <li>• easy camera mounting</li> <li>• robust anodized surface</li> <li>• stable lightweight metal design (aluminium, 18 g)</li> </ul>

**Cable**

Article number	11702660
Name	cable USB 3.0 die-cast MicB (screw)/A, 3,0 m (KSG U2/KSGU6GC0300G)
Features	<ul style="list-style-type: none"> <li>• USB 3.0 interface cable with screwable Micro-B connector to USB 3.0 type A connector with screw lock option</li> <li>• both connectors with die-cast housing</li> <li>• length 3,0 m</li> </ul>

**Process interface cable**

Article number	11118810
----------------	----------

**Process interface cable**

Name	shielded cable 8 wires, 5,0 m (Z-ESG 32FP0500G)
Features	<ul style="list-style-type: none"> <li>• shielded cable</li> <li>• M8 female connector</li> <li>• 8-pin</li> <li>• open wires at one side</li> <li>• cable carrier compatible</li> <li>• length 5,0 m</li> </ul>

**Interface card**

Article number	11141165
Name	USB3.0 2 Port PCIe Card (ZVA-PCIe_2x_external_USB_3.0)
Features	<ul style="list-style-type: none"> <li>• 2 port USB 3.0 board</li> <li>• chipset: Renesas PD720202</li> <li>• tested bandwidth 2950Mbit/s</li> <li>• 1 lane PCIe plug board</li> <li>• tested driver version: Renesas 3.0.23.0</li> </ul>

2023-09-01 The product features and technical data specified do not express or imply any warranty. Technical modifications subject to change.