

Overview

- USB 3.0 PCIe interface board (2 ports)
- USB 3.0 cable, 3,0 m
- process interface cable 5,0 m
- Mounting Adapter Type E
- Software (WINDOWS, LINUX, LINUX ARM) via Download
- camera not included



Technical data

Fixing

Article number	11165173
Name	Mounting Adapter Type E
Features	<ul style="list-style-type: none"> • easy camera mounting • robust anodized surface • stable lightweight metal design (aluminium, 18 g)

Cable

Article number	11702660
Name	cable USB 3.0 die-cast MicB (screw)/A, 3,0 m (KSG U2/KSGU6GC0300G)
Features	<ul style="list-style-type: none"> • USB 3.0 interface cable with screwable Micro-B connector to USB 3.0 type A connector with screw lock option • both connectors with die-cast housing • length 3,0 m

Process interface cable

Article number	11118810
----------------	----------

Process interface cable

Name	shielded cable 8 wires, 5,0 m (Z-ESG 32FP0500G)
Features	<ul style="list-style-type: none"> • shielded cable • M8 female connector • 8-pin • open wires at one side • cable carrier compatible • length 5,0 m

Interface card

Article number	11141165
Name	USB3.0 2 Port PCIe Card (ZVA-PCIe_2x_external_USB_3.0)
Features	<ul style="list-style-type: none"> • 2 port USB 3.0 board • chipset: Renesas PD720202 • tested bandwidth 2950Mbit/s • 1 lane PCIe plug board • tested driver version: Renesas 3.0.23.0