

**overview**

- 10-GigE PCIe interface board
- GigE cable 5,0 m (M12/x-coded)
- Power Supply 24 V/1.0 A with adapter cable M12/12-pin to DC connector
- Tube system M62 with adapter (11193125) and tube (11185374)
- Mounting Adapter Type C
- Heat Sink Type B
- camera not included



**technical data**

**fixing**

article number	11053252
name	Mounting Adapter Type C
features	<ul style="list-style-type: none"> <li>• easy camera sidewise mounting</li> <li>• robust anodized surface</li> <li>• stable lightweight metal design (aluminium, 61g)</li> </ul>

**cable**

article number	11101979
name	cable GigE M12X/RJ45, 5,0 m
features	<ul style="list-style-type: none"> <li>• GigE cable</li> <li>• M12/x-coded connector to RJ45</li> <li>• length 5,0 m</li> </ul>

**heat sink kit**

article number	11114702
name	Heat Sink Type B
components	<ul style="list-style-type: none"> <li>• heat sink for VLXT cameras</li> </ul>

**process interface cable**

article number	11201118
name	shielded cable 12 wires, 2,0 m (ESG 34JP0200GS)
features	<ul style="list-style-type: none"> <li>• shielded cable</li> <li>• M12/12-pin female connector</li> <li>• open wires at one side</li> <li>• cable carrier compatible</li> <li>• length 2,0 m</li> </ul>

**interface card**

article number	11190893
name	10-GigE Server Adapter X550-T2 (ZVA-Intel_X550-T2_10GbE_Serv_Adapter)
features	<ul style="list-style-type: none"> <li>• 2 port GigE to PCI Express host adapter</li> <li>• RJ45 connector</li> <li>• chipset: Intel® iX550 Ethernet Controller</li> <li>• tested Jumbo Frames: 9 kByte</li> <li>• x4 lane interface</li> </ul>

**power supply**

article number	11079750
name	Power Supply 24V/1.0A Int. DC Connec
features	<ul style="list-style-type: none"> <li>• power supply 24V/1000mA</li> <li>• adapter for EU, US, UK, AU and KR</li> </ul>

**power cable**

article number	11048083
name	cable Power Adapter M12/DC Connector
features	<ul style="list-style-type: none"> <li>• adapter cable M12/12-pin to DC connector</li> <li>• length 2.0 m</li> </ul>