Baumer
Passion for Sensors

Starter kits

VLXT.FO Starter Kit

Article number: 11213910

overview

- Fiber PCIe Interface Board
- SFP+ 10-GigE cable 5,0 m
- Process interface cable 2,0 m
- Power Supply 24 V/1.0 A with adapter cable M12/12-pin to DC connector
- Tube system M62 with adapter (11193125) and tube (11185374)
- Mounting Adapter Type C
- Heat Sink Type B
- camera not included

technical data

fixing	
article number	11053252
name	Mounting Adapter Type C
description	• easy camera sidewise mounting • robust anodized surface • stable lightweight metal design (aluminium, 61g)

cable	
article number	11700591
name	10-GigE DA Cable Copper SFP+/SFP+, 5.0m
description	• SFP+ (direct attached) • length 5.0 m

heat sink kit	
article number	11114702
name	Heat Sink Type B
components	• heat sink for VLXT cameras

process interface cable	
article number	11201118
name	shielded cable 12 wires, 2.0 m (ESG 34JP0200GS)
description	• shielded cable • M12/12-pin female connector • open wires at one side • cable carrier compatible • length 5,0 m

interface card	
article number	11700594
name	ZVA-DeLock_PCIe_Fiber_SFP+_10-GigE
description	• 1 port SFP+ • chipset: Tehuti TN4010 Controller • supported Jumbo Frames: 16 kByte • x4 lane interface

power supply	
article number	11079750
name	Power Supply 24V/1.0A Int. DC Connec
description	• power supply 24V/1000mA • adapter for EU, US, UK, AU and KR

power cable	
article number	11048083
name	cable Power Adapter M12/DC Connector
description	• adapter cable M12/12-pin to DC connector • length 2.0 m

2020-01-30 The product features and technical data specified do not express or imply any warranty. Technical modifications subject to change.