

## ZVL-Canon\_EF\_50mm f/1.8\_STM

Article number: 11703230

### Overview

- Canon lens
- 50 mm
- f 1.8 - 22
- format 43 mm
- STM auto focus (focus control: manual/automatic)
- Canon EF-mount



### Technical data

General data		Lens data	
Manufacturer	Canon	Lens resolution	65 MP
Mechanical data		Focal length	50 mm
Lens mount	Canon EF-mount	Focal range	≥ 50 mm
Dimensions	69.2 mm × 39.3 mm	Format	43 mm
Max. outer diameter	70 mm (without knurled screws)	Aperture	f 1,8 - 22
Max. length (excl. thread)	39.3 mm	Aperture control	manual / automatic
Weight	≤ 160 g	Horizontal angle of view	40 °
Filter thread	M 49	Vertical angle of view	27 °
		Diagonal angle of view	46 °