


Overview

- Carl Zeiss lens
- 18 mm
- F 2,0-22
- format 4/3"
- M.O.D. 0,090 m
- locating screw for aperture and focus
- C-mount



Technical data

General data

Manufacturer Carl Zeiss

Mechanical data

Lens mount C-mount

Dimensions 57 mm × 66 mm

Max. outer diameter 57 mm (without knurled screws)
63 mm (with knurled screws)

Max. length (excl. thread) 66 mm

Weight ≤ 291 g

Filter thread M 43,0 × 0,75

Lens data

Lens resolution 20 MP

Pixel resolution 2 μm

Focal length 18 mm

Focal range ≥ 12 mm ... < 25 mm

Format 4/3"

Aperture F2,0-22

Aperture control Manual

M.O.D. 0.09 m

Environmental conditions

Operating temperature -22 ... +55 °C