

Overview

- Carl Zeiss lens
- 35 mm
- F 2,0-22
- format 4/3"
- M.O.D. 0,209 m
- locating screw for aperture and focus
- C-mount



Technical data

General data

Manufacturer Carl Zeiss

Mechanical data

Lens mount C-mount

Dimensions 57 mm × 70 mm

Max. outer diameter 57 mm (without knurled screws)
70 mm (with knurled screws)

Max. length (excl. thread) 70 mm

Weight ≤ 323 g

Filter thread M 49,0 × 0,75

Lens data

Lens resolution 20 MP

Pixel resolution 2 μm

Focal length 35 mm

Focal range ≥ 25 mm ... < 50 mm

Format 4/3"

Aperture F2,0-22

Aperture control Manual

M.O.D. 0.209 m

Environmental conditions

Operating temperature -22 ... +55 °C