

overview

- Carl Zeiss lens
- 8 mm
- F 2,8-22
- format 4/3"
- M.O.D. 0,102 m
- locating screw for aperture and focus
- C-mount



technical data

general data

manufacturer Carl Zeiss

mechanical data

lens mount C-mount

dimensions 86 mm × 63 mm

max. outer diameter 86 mm (without knurled screws)
86 mm (with knurled screws)

max. length (excl. thread) 63 mm

weight ≤ 376 g

filter thread M 72,0 × 0,75

lens data

lens resolution 20 MP

focal length 8 mm

focal range < 12 mm

format 4/3"

aperture F2,8-22

aperture control manual

M.O.D. 0,102 m

environmental conditions

operating temperature -22 ... +55 °C