

Overview

- Evetar lens
- 5,4 mm
- F 2,8
- format 1/2,3"
- M.O.D. 0,3 m
- IR Cut Filter
- S-mount



Technical data

General data

Manufacturer Evetar

Mechanical data

Lens mount S-mount

Dimensions 13,5 mm × 18,74 mm

Max. length (excl. thread) 4.3 mm

Weight ≤ 6 g

Lens data

Lens resolution 10 MP

Focal length 5.4 mm

Focal range < 12 mm

Lens data

Format 1/2.3"

Aperture F2,8

Aperture control fix

M.O.D. 0.3 m

Horizontal angle of view 60.5 °

Vertical angle of view 32.2 °

Diagonal angle of view 72.4 °

At image format 6,2 × 3,1 mm

Environmental conditions

Operating temperature -20 ... +50 °C