

ZVL-FL-BC1218A-VG

Article number: 11006550

Overview

- Ricoh Imaging lens
- 12,5 mm
- F 1,8-C
- format 1"
- M.O.D. 0,3 m
- locating screw for aperture and focus
- C-mount



Technical data

General data

Manufacturer Ricoh Imaging

Mechanical data

Lens mount C-mount

Dimensions 42 mm × 50 mm

Max. outer diameter 42 mm (without knurled screws)
52 mm (with knurled screws)

Max. length (excl. thread) 50 mm

Weight ≤ 95 g

Filter thread M 40,5 × 0,5

Lens data

Lens resolution 0.3 MP

Focal length 12.5 mm

Lens data

Focal range ≥ 12 mm ... < 25 mm

Format 1"

Aperture F1,8-C

Aperture control Manual

M.O.D. 0.3 m

Horizontal angle of view 55.5 °

Vertical angle of view 42.6 °

Diagonal angle of view 67.2 °

At image format 12,7 × 9,5 mm

Environmental conditions

Operating temperature -20 ... +50 °C